


Monteringsplade | Vægskabe, AMP

Stålmonteringspladen bidragertil, at samlingen af skabet kan foregå hurtigere, da den nemt kan bearbejdes og udstyres med komponenter inden montering.



FUNKTIONER

Beskrivelse: Monteringsplade i stål til vægskabe. Alle størrelser fra 800 mm og derover styrkes af ombukkede kanter. Ved hjælp af AMG-tilbehøret, kan monteringspladepositionen justeres til enhver dybde. Dette tilbehør er ikke egnet til AFS-skabsserien. Se venligst udskiftnings- og reservedelskataloget.

Materiale: Galvaniseret stål.

Pakke størrelse: 1 stk.

Materiale: Lakeret Stål
Finish: Galvaniseret
Tykkelse: 2mm

SPECIFIKATIONER

Table 1/2

Katalognummer	Højde	Bredde	Dybde	Panelstørrelse	Enclosure Material
AMP10100	1000mm	999mm	12mm	970 x 950mm	Lakeret Stål
AMP10120	1000mm	1199mm	12mm	970 x 950mm	Lakeret Stål
AMP12120	1200mm	1199mm	12mm	1170 x 1150mm	Lakeret Stål
AMP02020	200mm	199mm	2mm	170 x 150mm	Lakeret Stål
AMP02520	250mm	199mm	2mm	220 x 150mm	Lakeret Stål
AMP02525	250mm	249mm	2mm	220 x 200mm	Lakeret Stål
AMP03025	300mm	249mm	2mm	270 x 200mm	Lakeret Stål
AMP03030	300mm	299mm	2mm	270 x 250mm	Lakeret Stål
AMP03040	300mm	400mm	2mm	270 x 350mm	Lakeret Stål
AMP03060	300mm	599mm	2mm	270 x 550mm	Lakeret Stål
AMP03080	300mm	799mm	2mm	270 x 750mm	Lakeret Stål
AMP03100	300mm	999mm	12mm	270 x 950mm	Lakeret Stål

Katalognummer	Højde	Bredde	Dybde	Panelstørrelse	Enclosure Material
AMP03120	300mm	1199mm	12mm	270 x 1150mm	Lakeret Stål
AMP03525	350mm	249mm	2mm	320 x 200mm	Lakeret Stål
AMP04030	400mm	299mm	2mm	370 x 250mm	Lakeret Stål
AMP04040	400mm	400mm	2mm	370 x 350mm	Lakeret Stål
AMP04050	400mm	500mm	2mm	370 x 450mm	Lakeret Stål
AMP04060	400mm	599mm	2mm	370 x 550mm	Lakeret Stål
AMP05030	500mm	299mm	2mm	470 x 250mm	Lakeret Stål
AMP05040	500mm	350mm	2mm	470 x 350mm	Lakeret Stål

Table 2/2

Katalognummer	Højde	Bredde	Dybde	Panelstørrelse	Enclosure Material
AMP05050	500mm	500mm	2mm	470 x 450mm	Lakeret Stål
AMP06040	600mm	400mm	2mm	570 x 350mm	Lakeret Stål
AMP06050	600mm	500mm	2mm	570 x 450mm	Lakeret Stål
AMP06060	600mm	599mm	2mm	570 x 550mm	Lakeret Stål
AMP06080	600mm	799mm	2mm	570 x 750mm	Lakeret Stål
AMP07050	700mm	500mm	2mm	670 x 450mm	Lakeret Stål
AMP08040	800mm	400mm	12mm	770 x 350mm	Lakeret Stål
AMP08060	800mm	599mm	12mm	770 x 550mm	Lakeret Stål
AMP08080	800mm	799mm	12mm	770 x 750mm	Lakeret Stål
AMP08120	800mm	1199mm	12mm	770 x 1150mm	Lakeret Stål
AMP10060	1000mm	599mm	12mm	970 x 550mm	Lakeret Stål
AMP10080	1000mm	799mm	12mm	970 x 750mm	Lakeret Stål
AMP12060	1200mm	599mm	12mm	1170 x 550mm	Lakeret Stål
AMP12080	1200mm	799mm	12mm	1170 x 750mm	Lakeret Stål
AMP12100	1200mm	999mm	12mm	1170 x 950mm	Lakeret Stål
AMP14100	1400mm	999mm	12mm	1370 x 950mm	Lakeret Stål

YDERLIGERE PRODUKTOPLYSNINGER

Ikke velegnet til AFS.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.