


Udvendig monteringsprofil | Gulvskabe, CLPO



En standardløsning, som er kompatibel med nVent HOFFMANs standardhulmønster, hvilket forenkler indkøb og montering.

FUNKTIONER

Beskrivelse: Universalprofil til både dybde og bredde på 25 mm DIN-hulmønsteret på skabsrammen. Den 75 mm brede profil er udstyret med tre rækker af huller, hvoraf den ene er drejet 90°. Dette gør det muligt at montere CLPO-profiler i begge retninger. CLPO øger den brugbare plads med 25 mm.

Materiale: 1.5 mm forzinket stål.

Pakke størrelse: 4 profiler.

Materiale: Lakeret Stål
Finish: Galvaniseret
Tykkelse: 1.5mm

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Load Rating	Enclosure Material
CLPO1000	74mm	43mm	911mm	1400N	Lakeret Stål
CLPO1200	74mm	43mm	1111mm	1200N	Lakeret Stål
CLPO300	74mm	43mm	211mm	2400N	Lakeret Stål
CLPO400	74mm	43mm	311mm	2400N	Lakeret Stål
CLPO500	74mm	43mm	411mm	2400N	Lakeret Stål
CLPO600	74mm	43mm	511mm	2400N	Lakeret Stål
CLPO800	74mm	43mm	711mm	1800N	Lakeret Stål

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.