

Partiel dør til monitor, DPM



Denne glaserede deldør er en praktisk løsning, når en computerskærm skal monteres inde i et skab. Døren sikrer din computerskærm mod tyveri og farer, som skyldes det omgivende miljø.

FUNKTIONER

Beskrivelse: Til monitor skærme fra 14" til 21". Bruges i kombination med den hængslede tastaturbakke DPK. Muliggør installation af en PC i ethvert gulvskab. Den resterende plads vil blive udfyldt med DPC top- og bundpaneler og DP partielle døre.

Materiale: 1.75 mm stålplade, synsområde: 4 mm sikkerhedsglas.

Overfladebehandling: RAL 7035 struktur pulvermaling.

Tæthedsgrad: IP 44.

Pakke størrelse: 1 dør med hængsler og dobbelt-bit 3 mm lås.

Monteringskrav: Anvendes i kombination med DPK tastaturbakke. Anbefales i kombination med CDH for at undgå hul mellem de øvre og nedre paneler.

Materiale: Lakeret Stål
Finish: Struktur Pulvermaling
Farve: Light Gray
Farvekode: RAL 7035

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Antal låse	Window Size	Produktfamilie
DPM0506R5	500mm	600mm	17mm	2	360 x 455mm	Free-Standing
DPM0606R5	600mm	600mm	17mm	2	460 x 455mm	Free-Standing

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.