

Plastisk kabelforskruning | Vægskabe, CPG



Komprimeringen af hvert kabel, der er monteret i denne kabelforskruning, kan justeres og fastgøres ved hjælp af en kontramøtrik, som giver trækaflastning samt høj beskyttelse mod indtrængen.

FUNKTIONER

Beskrivelse: Traditionelle kabel fittings. Kabelforskruning med høj beskyttelsesgrad. Plastic låsemøtrikker til montering er inklusiv i levering.

Materiale: Polyamid PA6 og pakning af neopren.

Temperaturområde: -20 °C til +100 °C.

Brændbarhed: V-2 iht. UL94.

Overfladebehandling: RAL 7035.

Tæthedsgrad: IP 66

Materiale: Polyamide 6; Neoprene

Finish: Smooth

Farve: Light Gray

Farvekode: RAL 7035

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Enclosure Material	Produktfamilie	Thread Size
CPG12	31mm	15mm	17mm	Lakeret Stål	Wall Mounted	M12 x 1.5
CPG16	40mm	22mm	24mm	Lakeret Stål	Wall Mounted	M16 x 1.5
CPG20	40mm	24mm	26mm	Lakeret Stål	Wall Mounted	M20 x 1.5
CPG25	46mm	33mm	35mm	Lakeret Stål	Wall Mounted	M25 x 1.5

Katalognummer	Højde	Bredde	Dybde	Enclosure Material	Produktfamilie	Thread Size
CPG32	56mm	42mm	44mm	Lakeret Stål	Wall Mounted	M32 x 1.5
CPG40	68mm	53mm	55mm	Lakeret Stål	Wall Mounted	M40 x 1.5
CPG50	71mm	60mm	62mm	Lakeret Stål	Wall Mounted	M50 x 1.5
CPG63	71mm	65mm	67mm	Lakeret Stål	Wall Mounted	M63 x 1.5

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.