

Sidedøre, DNS



En sidedør monteret på et skab giver nem adgang fra siderne til det udstyr, der er monteret foran og bagpå. Dette er særligt fordelagtigt, hvis der anvendes monteringsplader, som monteres ryg mod ryg.

FUNKTIONER

Beskrivelse: Erstatning for sidepanelet SPM. For let adgang til udstyr inde i kabinettet, eller når skabe er monteret bagende mod bagende. Udstyret med standard dobbelt-bit 3 mm lås, som åbner alle låsemuligheder. Dørramme valgfri.

Materiale: 2 mm stålplade.

Overfladebehandling: RAL 7035 struktur pulvermaling.

Tæthedsgad: Overholder IP 55 | TYPE 12 | IK 10.

Pakke størrelse: 1 dør inklusive monteringsramme.

Materiale:	Lakeret Stål
Finish:	Struktur Pulvermaling
Farve:	Light Gray
Farvekode:	RAL 7035
Tykkelse:	2mm

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Produktfamilie	Enclosure Material
DNS1805R5	1782mm	493mm	51mm	Free-Standing	Lakeret Stål
DNS1806R5	1782mm	593mm	51mm	Free-Standing	Lakeret Stål
DNS2005R5	1982mm	493mm	51mm	Free-Standing	Lakeret Stål
DNS2006R5	1982mm	593mm	51mm	Free-Standing	Lakeret Stål

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.