


Sidepaneler | Gulvskabe, SPM



Disse sidepaneler sikrer, at beskyttelse mod indtrængen opretholdes, hvilket betyder, at de elektriske komponenter kan fungere uden forstyrrelser, samt at personalet beskyttes mod skader.

FUNKTIONER

Beskrivelse: Enkel montering. Forseglet med en ekstruderet polyuretanpakning i ét stykke og monteret med 8 skruer og nye patenterede holdere. Kan erstattes af DNS sidedør.

Materiale: 1.5 mm stålplade.

Overfladebehandling: RAL 7035 struktur pulvermaling.

Tæthedegrad: IP 55 | TYPE 12, 13 i kombination med MCS. IP66 | TYPE 4, 12, 13 i kombination med MCS-HP.

Pakke størrelse: 2 paneler med monteringstilbehør.

Finish: Struktur Pulvermaling
Farvekode: RAL 7035
Tykkelse: 1.5mm

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Farve	Produktfamilie	Enclosure Material
SPM1805R5	1800mm	19mm	500mm	Light Gray	Free-Standing	Lakeret Stål
SPM1804R5	1800mm	19mm	400mm	Light Gray	Free-Standing	Lakeret Stål
SPM1806R5	1800mm	19mm	600mm	Light Gray	Free-Standing	Lakeret Stål
SPM2005R5	2000mm	19mm	500mm	Light Gray	Free-Standing	Lakeret Stål
SPM2004R5	2000mm	19mm	400mm	Light Gray	Free-Standing	Lakeret Stål
SPM2006R5	2000mm	19mm	600mm	Light Gray	Free-Standing	Lakeret Stål
SPM2008R5	2000mm	19mm	800mm	Light Gray	Free-Standing	Lakeret Stål
SPM2206R5	2200mm	19mm	600mm	Light Gray	Free-Standing	Lakeret Stål
SPM2208R5	2200mm	19mm	800mm	Light Gray	Free-Standing	Lakeret Stål
SPM1106R5	1100mm	19mm	600mm	Light Gray	Free-Standing	Lakeret Stål
SPM1406R5	1400mm	19mm	600mm	Light Gray	Free-Standing	Lakeret Stål
SPM1606R5	1600mm	19mm	600mm	Light Gray	Free-Standing	Lakeret Stål
SPM1808R5	1800mm	19mm	800mm	Light Gray	Free-Standing	Lakeret Stål

Katalognummer	Højde	Bredde	Dybde	Farve	Produktfamilie	Enclosure Material
SPM2010R5	2000mm	19mm	1000mm	Light Gray	Free-Standing	Lakeret Stål
SPM1205R5	1200mm	19mm	500mm	Light Grey	Free-Standing	Lakeret Stål
SPM1405R5	1400mm	19mm	500mm	Light Gray	Free-Standing	Lakeret Stål
SPM1605R5	1600mm	19mm	500mm	Light Gray	Free-Standing	Lakeret Stål
SPM1810R5	1800mm	19mm	1000mm	Light Gray		Lakeret Stål
SPM2210R5	2200mm	19mm	1000mm	Light Gray		Lakeret Stål

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.