

Sidepanel rustfrit stål, SPMS



Disse sidepaneler sikrer, at beskyttelse mod indtrængen opretholdes, hvilket betyder, at de elektriske komponenter kan fungere uden forstyrrelser, samt at personalet beskyttes mod skader.

FUNKTIONER

Beskrivelse: Enkel montering. Forseglet med en ekstruderet polyuretanpakning i ét stykke og monteret med 8 skruer og nye patenterede holdere.

Tæthedsgad: IP 55 | TYPE 12, 13 i kombination med MCSS. IP66 | TYPE 4X, 12 i kombination med MCSS-HP.

Pakke størrelse: 2 paneler inkl monteringsmateriale.

Materiale: 1.5 mm AISI 304 / AISI 316L slebet rustfrit stål.

Overfladebehandling: 400 slebet rustfrit stål.

Finish: Poleret

Tykkelse: 1.5mm

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Produktfamilie	Enclosure Material	Materiale
SPMS1805	1764mm	18mm	462mm	Free-Standing	Stainless Steel	Stainless Steel 304
SPMS2006	1964mm	18mm	562mm	Free-Standing	Stainless Steel	Stainless Steel 304
SPMS1805-316	1764mm	18mm	462mm	Free-Standing	Stainless Steel	Stainless Steel 316
SPMS2006-316	1964mm	18mm	562mm	Free-Standing	Stainless Steel	Stainless Steel 316
SPMS1804	1764mm	18mm	400mm	Free-Standing	Stainless Steel	Stainless Steel, 304
SPMS1804-316	1764mm	18mm	400mm	Free-Standing	Stainless Steel	Stainless Steel, 316

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.