


Split bundplade rustfrit stål, CBPS



Et delt bundplade tilbyder en fleksibel løsning til kabelføring og eliminerer behovet for individuelle kabelforskruninger. Beskyttelsesgraden opretholdes ved hjælp af en separat pakning.

FUNKTIONER

Beskrivelse: Monteres i stedet for standard bundplade i i ét stykke. Tillader direkte kabelindføring. For at opnå perfekt forsegling omkring kablerne, anvendes BG01 pakningssæt.

Materiale: AISI 304 / 316L slebet rustfrit stål.

Bundplader: 1.5 mm.

Overfladebehandling: 400 slebet rustfrit stål.

Pakke størrelse: 1 sæt af 2 bundplader.

Finish: Poleret

Tykkelse: 1.5mm

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Enclosure Material	Materiale
CBPS0640	25mm	600mm	400mm	Stainless Steel	Stainless Steel 304
CBPS0640-316	25mm	600mm	400mm	Stainless Steel	Stainless Steel 316
CBPS0650	25mm	600mm	500mm	Stainless Steel	Stainless Steel 304
CBPS0650-316	25mm	600mm	500mm	Stainless Steel	Stainless Steel 316
CBPS0660	25mm	600mm	600mm	Stainless Steel	Stainless Steel 304
CBPS0660-316	25mm	600mm	600mm	Stainless Steel	Stainless Steel 316
CBPS0840	25mm	800mm	400mm	Stainless Steel	Stainless Steel 304
CBPS0840-316	25mm	800mm	400mm	Stainless Steel	Stainless Steel 316
CBPS0850	25mm	800mm	500mm	Stainless Steel	Stainless Steel 304
CBPS0850-316	25mm	800mm	500mm	Stainless Steel	Stainless Steel 316
CBPS0860	25mm	800mm	600mm	Stainless Steel	Stainless Steel 304
CBPS0860-316	25mm	800mm	600mm	Stainless Steel	Stainless Steel 316
CBPS1040	25mm	1000mm	400mm	Stainless Steel	Stainless Steel 304
CBPS1040-316	25mm	1000mm	400mm	Stainless Steel	Stainless Steel 316

Katalognummer	Højde	Bredde	Dybde	Enclosure Material	Materiale
CBPS1050	25mm	1000mm	500mm	Stainless Steel	Stainless Steel 304
CBPS1050-316	25mm	1000mm	500mm	Stainless Steel	Stainless Steel 316
CBPS1060	25mm	1000mm	600mm	Stainless Steel	Stainless Steel 304
CBPS1060-316	25mm	1000mm	600mm	Stainless Steel	Stainless Steel 316

YDERLIGERE PRODUKTOPLYSNINGER

For skabe 1200 mm & 1600 mm bredde anvendes 2x600 mm & 2x800 mm bundplader.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.