

Ventilerede top- og bundpaneler | Gulvskabe, DPCV

Både skabets udseende og IP-klassificering opretholdes, når et komplet sæt døre og paneler er monteret. Ventilationspanelerne giver desuden naturlig ventilation.



FUNKTIONER

Beskrivelse: Benyttes til dækning af resterende plads i top og bund. Ventilationsslidser til ekstra varmeafledning i skabe med koblingsudstyr. Bruges i kombination med vandrette deleskinner CDH/CDHK

Materiale: 1.75 mm stålplade.

Overfladebehandling: RAL 7035 struktur pulvermaling.

Tæthedsgrad: IP 20.

Monteringskrav: DPCV dækker 200 mm i højden af skabet. Så for et 2000 mm højt kabinet når DPCV bruges, er der 1800 mm plads tilbage til partielle døre/paneler.

Pakke størrelse: 2 paneler med monteringsmateriale.

Materiale:	Lakeret Stål
Finish:	Struktur Pulvermaling
Farve:	Light Gray
Farvekode:	RAL 7035
Tykkelse:	1.75mm

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Height 1	Height 2	Produktfamilie
DPCV0714R5	104mm	400mm	17mm	70mm	100mm	Free-Standing

Katalognummer	Højde	Bredde	Dybde	Height 1	Height 2	Produktfamilie
DPCV0716R5	104mm	600mm	17mm	70mm	100mm	Free-Standing
DPCV0718R5	104mm	800mm	17mm	70mm	100mm	Free-Standing

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.