

Glasdøre, ADC



De elektriske komponenter kan ses, når døren er lukket, hvilket holder uautoriseret personale ude og opretholder beskyttelsen mod indtrængning.

FUNKTIONER

Beskrivelse: Til erstatning af standarddøren. Viser tydeligt de komponenter, som er installeret inde i skabet. Kan bruges med alt udstyr fra låseprogrammet.

Materiale: 1.2 mm lakeret stål / 1.5 mm for skabe med en højde eller bredde 500 mm eller større / 2 mm til skabe med en højde eller bredde på 800 mm eller derover, samt 4 mm klart sikkerhedsglas.

Overfladebehandling: RAL 7035 struktur pulvermaling.

Tæthedsgrad: Er i overensstemmelse med IP 55 | TYPE 12, 13, IK 07.

Pakke størrelse: 1 stk.

Materiale: Lakeret Stål
Finish: Struktur Pulvermaling
Farve: Light Gray
Farvekode: RAL 7035

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Tykkelse	Antal låse	Window Size
ADC03025R5	300mm	250mm	15mm	1.2mm	1	159 x 93mm
ADC03030R5	300mm	300mm	15mm	1.2mm	1	159 x 143mm
ADC04030R5	400mm	300mm	15mm	1.2mm	1	259 x 143mm
ADC04040R5	400mm	400mm	15mm	1.2mm	1	259 x 243mm
ADC05030R5	500mm	300mm	15mm	1.5mm	1	359 x 143mm
ADC05040R5	500mm	400mm	15mm	1.5mm	1	359 x 243mm
ADC06040R5	600mm	400mm	15mm	1.5mm	2	459 x 243mm
ADC06050R5	600mm	500mm	15mm	1.5mm	2	459 x 343mm
ADC06060R5	600mm	600mm	15mm	1.5mm	2	459 x 443mm
ADC07050R5	700mm	500mm	15mm	1.5mm	2	559 x 343mm
ADC08060R5	800mm	600mm	15mm	2mm	2	659 x 443mm
ADC10060R5	1000mm	600mm	15mm	2mm	1	859 x 427mm

Katalognummer	Højde	Bredde	Dybde	Tykkelse	Antal låse	Window Size
ADC10080R5	1000mm	800mm	15mm	2mm	1	859 x 627mm
ADC12060R5	1200mm	600mm	15mm	2mm	1	1059 x 427mm
ADC12080R5	1200mm	800mm	15mm	2mm	1	1059 x 627mm

YDERLIGERE PRODUKTOPLYSNINGER

* 3-punkts espagnolet-lås. Ikke egnet til AFS.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.