


19" Front Panel for Thermostat With Digital Display, 1 U



19" Front Panel for Thermostat With Digital Display, 1 U

FUNKTIONER

19" Front Panel, 1 U, with cut-out for thermostat with digital display

Accessory Type: Front panel



SPECIFIKATIONER

Table 1/3

Katalognummer	Type	Mounting	EMC Shielding	Materiale	Front Finish	Rear Finish
30118-267	19" Front Panel	Screw-on Front	No	Aluminium	Anodized	Anodized
30118-315	19" Front Panel	Screw-on Front	No	Aluminium	Painted	Painted
30118-360	19" Front Panel	Screw-on Front	No	Aluminium	Painted	Painted

Table 2/3

Katalognummer	Farvekode	Rack Height	Højde	Rack Width	Bredde	Dybde
30118-267		1U	35mm		76mm	3mm
30118-315	RAL 7035	1U	43mm	95HP	483mm	3mm
30118-360	RAL 7021	1U	43mm	95HP	483mm	3mm

Table 3/3

Katalognummer	Pakke mængde	Finish
30118-267	1	Anodized
30118-315	1	Struktur Pulvermaling

Katalognummer	Pakke mængde	Finish
30118-360	1	Struktur Pulvermaling

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.