


On Board Rack



Suitable for ongoing vibrations, shock, high temperatures, and high humidity.

FUNKTIONER

For mobile railway applications

Suitable for ongoing vibrations, shock, high temperatures, and high humidity

Suitable for 1, 2, or 3 U SNCF subracks (NF F61-005, CF 60-002)

Rear side is equipped for standard connectors; crossbar can be custom-coded for the SNCF coding pins

Crossbar with integrated cable channel

Several racks can be stacked or fitted in rows

Produced using a welding process, certified to EN 15085 (CL2)

Stainless Steel welds passivated to prevent corrosion

Dybde:	341.8mm
Finish:	Raw
Complies With:	SNCF NFF 61005; SNCF NFF 60002
Frame Material:	Stainless Steel
Static Load:	25kg
Product Type:	Rack



SPECIFIKATIONER

Katalognummer	Rack Height	Højde	Bredde	Pakke mængde	Materiale	Rack Width
10170-012	6U	290mm	496.4mm	1	Stainless Steel	84HP
10170-013	6U	290mm	252.65mm	1	Stainless Steel	36HP
10170-014	3U	156.7mm	496.4mm	1	Stainless Steel	84HP
10170-015	3U	156.7mm	252.65mm	1	Stainless Steel	36HP
10170-016	9U	423.4mm	496.4mm	1	Stainless Steel	84HP
10170-017	9U	423.4mm	252.65mm	1	Stainless Steel	36HP

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.