


Countersunk Screw



Flush surface, no interference with sliding parts. Self-centering in precision countersink. Clean external geometry (important for hygiene or airflow).

FUNKTIONER

Countersunk screws are used for numerous mounting options in a subrack or desktop case.

Cross Recess imprint offers a high level of torque to achieve quick and easy installation

Torx imprint bears greater torque

The Torx star-shaped head prevents cam-out

Product Type: Screw



SPECIFIKATIONER

Table 1/2

Katalognummer	Length	Materiale	Finish	Pakke mængde	Thread Size	Højde
24560-182	12mm	Stål	Forzinket Stål	4	M5	
24560-183	12mm	Stål	Forzinket Stål	100	M5	
21100-429	8mm	Stål	Nickel Plated	100	M2.5	
21100-507	12mm	Stål	Nickel Plated	100	M2.5	
21100-500	10mm	Stål	Nickel Plated	100	M2.5	
21100-542	8mm	Stål	Nickel Plated	100	M3	
21100-649	10mm	Stål	Zinc Plated, Black	100	M2.5	
24560-139	5mm	Stål	Forzinket Stål	100	M4	
24560-145	14mm	Stål	Forzinket Stål	100	M4	
24560-158	7.7mm	Stål	Forzinket Stål	100	M2.5	
24560-164	8mm	Stål	Nickel Plated	100	M2.5	4.7mm

Table 2/2

Katalognummer	Type	Bredde	Works With	Thread Length	Thread Type	Torque
24560-182	Countersunk Screw		Front Panels	12mm		2.3N·m
24560-183	Countersunk Screw		Front Panels	12mm		2.3N·m

Katalognummer	Type	Bredde	Works With	Thread Length	Thread Type	Torque
21100-429	Screw		Front Panels	8mm		0.3N·m
21100-507	Screw		Front Panels	12mm		0.3N·m
21100-500	Screw		Front Panels	10mm		0.3N·m
21100-542	Screw		Front Panels	8mm		0.35N·m
21100-649	Screw		Front Panels	10mm		0.3N·m
24560-139	Countersunk Screw		Front Panels	5mm		1.2N·m
24560-145	Countersunk Screw		Front Panels	14mm		1.2N·m
24560-158	Countersunk Screw		Front Panels	7.7mm		0.3N·m
24560-164	Countersunk Screw	4.7mm	Front Panels	8mm	Metric	0.3N·m

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.