

DC Fan

Axial fan, 119 mm, with DC input. Replacement part for 1 U fan trays.

FUNKTIONER

Axial 119 mm DC fan, with plug for connection cable



SPECIFIKATIONER

Table 1/2

Katalognummer	Works With	Bredde	Length	Højde	Spænding DC	Luftstrøm
20713-240	19" Fan Trays	119mm	119mm	38mm	24V	184m³/h
20713-172	19" Fan Trays	119mm	119mm	25.5mm	24V	171m³/h
20713-241	19" Fan Trays	119mm	119mm	38mm	12V	184m³/h
20713-242	19" Fan Trays	119mm	119mm	38mm	48V	184m³/h
60713-600	19" Fan Trays	119mm	119mm	32mm	12V	140m³/h

Table 2/2

Katalognummer	Noise Level	Power	Max Static Pressure	Omgivelsestemperatur	Pakke mængde
20713-240	42dB(A)	8W	68Pa	70°C	1
20713-172	50.5dB(A)	7W	50.5Pa	70°C	1
20713-241	42dB(A)	8W	68Pa	70°C	1
20713-242	42dB(A)	8W	68Pa	70°C	1
60713-600	39dB(A)	8W	46Pa	70°C	1

YDERLIGERE PRODUKTOPLYSNINGER

Please order connection cable and protective grille separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

