



$^{+/-}$ can be combined, $^{+/-}$ combinations not recommended

 Light profile	-	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile

34560-540

FUNKTIONER

< 28 HP not printed

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings



PRODUKTEGENSKABER

Rack Width: 40HP

Pakke mængde: 1

Finish: Anodized

Length: 208.28mm

Materiale: Aluminium

Produktfamilie: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Product Type: Horizontal Rail

Type: Heavy, ST

Works With: Subracks; Cases

Net Weight: 0.068kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YDERLIGERE PRODUKTOPLYSNINGER

Delivery is in standard pack multiples. Pricing is per individual item.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.