

EuropacPRO 19" Subrack Kit for Backplane, Retrofit Shielding

Non-shielded subrack for backplane mounting.



FUNKTIONER

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Rear horizontal rail for backplane mounting with insulation strip

Aluminum construction

IP 20, in accordance with IEC 60529

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

EMC Shielding: No
Finish: Anodized; Passivated
Product Type: Subrack/Chassis



SPECIFIKATIONER

Table 1/2						
Katalognummer	Rack Height	Dybde	Pakke mængde	For Mounting	Board Depth	Gasket Type
24563-131	3U	175m m	1	Backplane	160mm	Stainless Steel EMC (retrofittable)
24563-132	3U	235m m	1	Backplane	160mm, 220mm	Stainless Steel EMC (retrofittable)
24563-133	3U	295m m	1	Backplane	160mm, 220mm, 280mm	Stainless Steel EMC (retrofittable)
24563-134	3U	355m m	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC (retrofittable)
24563-135	3U	415m m	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC (retrofittable)
24563-136	3U	475m m	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC (retrofittable)
24563-431	6U	175m m	1	Backplane	160mm	Stainless Steel EMC (retrofittable)
24563-432	6U	235m m	1	Backplane	160mm, 220mm	Stainless Steel EMC (retrofittable)
24563-433	6U	295m m	1	Backplane	160mm, 220mm, 280mm	Stainless Steel EMC (retrofittable)
24563-434	6U	355m m	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC (retrofittable)
24563-435	6U	415m m	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC (retrofittable)
24563-436	6U	475m m	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC (retrofittable)

Table 2/2							
Katalognummer	Håndtag inkluderet	Mounting	Complies With	Materiale	Rack Width	Static Load	
24563-131	No	Rack	IEC 60297-3-103	Aluminium	84HP	11kg	
24563-132	No	Rack	IEC 60297-3-103	Aluminium	84HP	11kg	
24563-133	No	Rack	IEC 60297-3-103	Aluminium	84HP	11kg	
24563-134	No	Rack	IEC 60297-3-103	Aluminium	84HP	11kg	
24563-135	No	Rack	IEC 60297-3-103	Aluminium	84HP	11kg	
24563-136	No	Rack	IEC 60297-3-103	Aluminium	84HP	11kg	
24563-431	No	Rack	IEC 60297-3-103	Aluminium	84HP	11kg	
24563-432	No	Rack	IEC 60297-3-103	Aluminium	84HP	11kg	
24563-433	No	Rack	IEC 60297-3-103	Aluminium	84HP	11kg	
24563-434	No	Rack	IEC 60297-3-103	Aluminium	84HP	11kg	
24563-435	No	Rack	IEC 60297-3-103	Aluminium	84HP	11kg	

Katalognummer	Håndtag inkluderet	Mounting	Complies With	Materiale	Rack Width	Static Load
24563-436	No	Rack	IEC 60297-3-103	Aluminium	84HP	11kg

YDERLIGERE PRODUKTOPLYSNINGER

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.