

Guide Rail With Coding for CompactPCI/ VME64x, PC



New generation of With Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

FUNKTIONER

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to a optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

Optional ESD clip for an conductive contact between PCB and horizontal rail available

Storage temperature: from -40 °C ... 130 °C

Produktfamilie:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac
Product Type:	Guide Rail
Type:	Coding
Works With:	Subracks; Cases; 19" Chassis; Systems



SPECIFIKATIONER

Katalognummer	Board Depth	Groove Width	Farve	Materiale	Pakke mængde	Complies With	Finish
64568-089	160mm	2	Red	Fiber-Reinforced Plastic	1	EN 45545-2	
64568-090	160mm	2	Grey	Fiber-Reinforced Plastic	1	EN 45545-2	

Katalognummer	Board Depth	Groove Width	Farve	Materiale	Pakke mængde	Complies With	Finish
24568-331	280mm	2.5	Red, Silver	Fiber-Reinforced Plastic, Aluminium	10	EN 45545-2	Anodized
24568-332	340mm	2.5	Red, Silver	Fiber-Reinforced Plastic, Aluminium	10	EN 45545-2	Anodized
24568-341	280mm	2.5	Grey, Silver	Fiber-Reinforced Plastic, Aluminium	10	EN 45545-2	Anodized
24568-342	340mm	2.5	Grey, Silver	Fiber-Reinforced Plastic, Aluminium	10	EN 45545-2	
24568-356	160mm	2	Red	Fiber-Reinforced Plastic	10	EN 45545-2	
24568-357	70mm	2	Red	Fiber-Reinforced Plastic	10	EN 45545-2	
24568-358	160mm	2	Grey	Fiber-Reinforced Plastic	10	EN 45545-2	
24568-360	70mm	2	Grey	Fiber-Reinforced Plastic	10	EN 45545-2	
64568-085	70mm	2	Red	Fiber-Reinforced Plastic	1	EN 45545-2	
64568-086	70mm	2	Grey	Fiber-Reinforced Plastic	1	EN 45545-2	
64568-091	220mm	2	Red	Fiber-Reinforced Plastic	1	EN 45545-2	
64568-092	220mm	2	Grey	Fiber-Reinforced Plastic	1	EN 45545-2	
64568-111	220mm	2.5	Red, Silver	Fiber-Reinforced Plastic, Aluminium	1	EN 45545-2	
64568-109	160mm	2.5	Red, Silver	Fiber-Reinforced Plastic, Aluminium	1	EN 45545-2	
64568-110	160mm	2.5	Grey, Silver	Fiber-Reinforced Plastic, Aluminium	1	EN 45545-2	
64568-112	220mm	2.5	Grey, Silver	Fiber-Reinforced Plastic, Aluminium	1	EN 45545-2	

YDERLIGERE PRODUKTOPLYSNINGER

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

