


# Guide Rail Multi Piece, Mid-Piece Aluminium/Plastic Extrusion



Guide rail mid-piece for individual multi-piece guide rails out of plastic or Aluminium extrusion. Suitable for Standard, Accessory, 4.4" PCB types and end pieces with coding.

## FUNKTIONER

Middle profile for mounting guide rails for 2 mm groove width

2 plastic end pieces are required; these are pushed on to both ends of the middle profile

Guide rails can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Storage temperature: from -40 °C ... 130 °C

**Produktfamilie:** EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac  
**Product Type:** Guide Rail  
**Type:** Middle Section



## SPECIFIKATIONER

Table 1/2

| Katalognummer | Board Depth | Groove Width | Farve  | Materiale | Pakke mængde | Works With               |
|---------------|-------------|--------------|--------|-----------|--------------|--------------------------|
| 34560-891     | 160mm       | 2            | Silver | Aluminium | 1            | Subracks, Cases, Chassis |
| 34560-892     | 220mm       | 2            | Silver | Aluminium | 1            | Subracks, Cases, Chassis |
| 34560-893     | 280mm       | 2            | Silver | Aluminium | 1            | Subracks, Cases, Chassis |
| 34560-900     | 1000mm      | 2            | Silver | Aluminium | 1            | Subracks, Cases, Chassis |
| 34564-891     | 160mm       | 2            | Grey   | PVC       | 1            | Subracks, Cases, Chassis |
| 34564-892     | 220mm       | 2            | Grey   | PVC       | 1            | Subracks, Cases, Chassis |
| 34564-893     | 280mm       | 2            | Grey   | PVC       | 1            | Subracks, Cases, Chassis |
| 34564-900     | 1000mm      | 2            | Grey   | PVC       | 1            | Subracks, Cases, Chassis |

Table 2/2

| Katalognummer | Finish   | Farvekode |
|---------------|----------|-----------|
| 34560-891     | Anodized |           |

| Katalognummer | Finish   | Farvekode |
|---------------|----------|-----------|
| 34560-892     | Anodized |           |
| 34560-893     | Anodized |           |
| 34560-900     | Anodized |           |
| 34564-891     |          | RAL 7035  |
| 34564-892     |          | RAL 7035  |
| 34564-893     |          | RAL 7035  |
| 34564-900     |          | RAL 7035  |

## YDERLIGERE PRODUKTOPLYSNINGER

Delivery may be in Standard Pack Quantity (SPQ). Pricing is per individual item.

One guide rail consists of 1 pair of head pieces and 1 profile piece.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.