


# MTCA.4 Front Panel



AdvancedTCA front panel (stainless steel) for textile gasketing. Shielded filler modules are used to close unused slots.

## FUNKTIONER

In accordance with MicroTCA.1 and MicroTCA.4 specifications

Shielded filler modules are used to close unused slots

Can be screwed on; is supported on the guide rail

|                        |                 |
|------------------------|-----------------|
| <b>Accessory Type:</b> | Front panel     |
| <b>EMC Shielding:</b>  | Yes             |
| <b>Materiale:</b>      | Stainless Steel |
| <b>Produktfamilie:</b> | AdvancedMC      |
| <b>Product Type:</b>   | Front Panel     |
| <b>Type:</b>           | Front Panel     |



## SPECIFIKATIONER

Table 1/2

| Katalognummer | Højde   | Rack Width | Pakke mængde | Mounting       | Gasket Type | Front Finish |
|---------------|---------|------------|--------------|----------------|-------------|--------------|
| 21850-102     | 84.68mm |            | 1            | Screw-on Front | Textile EMC | Raw          |
| 21850-103     | 84.68mm |            | 1            | Screw-on Front | Textile EMC | Raw          |
| 20849-213     | 95mm    | 2HP        | 1            | Screw-on Front | Textile EMC | Raw          |
| 20849-214     | 170mm   | 2HP        | 1            | Screw-on Front | Textile EMC | Raw          |

Table 2/2

| Katalognummer | Rear Finish | Dybde | Bredde  |
|---------------|-------------|-------|---------|
| 21850-102     | Raw         | 1mm   | 18.96mm |
| 21850-103     | Raw         | 1mm   | 28.98mm |
| 20849-213     | Raw         | 0.6mm | 8.8mm   |
| 20849-214     | Raw         | 0.6mm | 8.8mm   |

## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

