


# Plug-In Unit Kit for FMC, Chromated, Shielded (Textile) With Handle



The FMC bezel are in accordance with Vita 57.1 specification. Covers the cut out in the overall front panel.

## FUNKTIONER

In accordance with Vita 57.1 specification

For single 69.0 x 76.5 mm or double 139.0 x 76.5 mm modules

Al-Profile plug-in unit with IEL handle

|                       |                               |
|-----------------------|-------------------------------|
| <b>EMC Shielding:</b> | Yes                           |
| <b>Finish:</b>        | Anodized; Passivated          |
| <b>Materiale:</b>     | Aluminium                     |
| <b>Product Type:</b>  | Front Panel                   |
| <b>Rack Width:</b>    | 4HP                           |
| <b>Type:</b>          | Front Panel with Handle (PIU) |



## SPECIFIKATIONER

Table 1/2

| Katalognummer | Rack Height | Pakke mængde | Håndtagstype | Mounting       | Gasket Type | Front Finish |
|---------------|-------------|--------------|--------------|----------------|-------------|--------------|
| 20836-253     | 3U          | 1            | IEL          | Screw-on Front | Textile EMC | Anodized     |
| 20836-254     | 6U          | 1            | IEL          | Screw-on Front | Textile EMC | Anodized     |

Table 2/2

| Katalognummer | Rear Finish | Treated Edges | Complies With            | Højde   | Bredde |
|---------------|-------------|---------------|--------------------------|---------|--------|
| 20836-253     | Conductive  | No            | FMC Mezzanine, Vita 57.1 | 128.4mm | 20mm   |
| 20836-254     | Conductive  | No            | FMC Mezzanine, Vita 57.1 | 261.8mm | 20mm   |

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl,

materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

