

Varistar CP Cabeling Rack



Welded steel frame for high static load requirements.
Prepared for high cable densities and 19" integration.

FUNKTIONER

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different Networking equipment possible

Integrated vertical and horizontal cable management

Can be easily integrated into aisle containment system

Frame Material: Stål
Materiale: Stål
Product Type: Rack

SPECIFIKATIONER

Table 1/2

Katalognummer	Rack Height	Cladding Material	Frame Color	Højde	Frame Color Code	Cladding Color
10630-027	42U	Stål	Black Grey	2000mm	RAL 7021	Black Grey
10630-028	42U	Stål	Black Grey	2000mm	RAL 7021	Black Grey

Table 2/2

Katalognummer	Bredde	Dybde	Static Load	Cladding Color Code	Pakke mængde	Dynamic Load	Finish
10630-027	800m m	1200m m	1600kg	RAL 7021	1	1000kgf	Struktur Pulvermaling
10630-028	800m m	1200m m	1600kg	RAL 7021	1	1000kgf	Struktur Pulvermaling

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

