

Wire Basket Tray Dropout 101X101 mm, ABS

KATALOGNUMMER

WBTCBLD04



The nVent CADDY Wire Basket Tray Drop Out is a versatile solution for creating cable management exits in cable tray. By acting as a wire funnel, the Drop Out enables cables to easily drop vertically from the tray while ensuring proper support and protecting the bend radius at the exit point. The tool-free design allows installers to drop the component into place on the wire basket tray while the side prongs hold it firmly in place. Whether contractors are working with multi-tier assemblies or side-by-side configurations, the Drop Out offers an aesthetic and efficient way to manage cable transitions, without compromising on performance or accessibility.

MERKMALE

Designed for center cable tray dropouts

Conducive to creating both multi-tier tray and side-by-side assemblies

Easily cut to fit around the wire basket tray for retrograde cable installations

Ensures the natural bend radius of the cable is protected

Stackable for multiple adjoining dropouts

Reusable and tool-free—easy-to-install, easy-to-remove

PRODUKTMERKMALE

Material: ABS, UL-VO zertifiziert


Oberfläche: Vorverzinkung

Höhe (H): 28.6 mm

Breite (W): 109.3 mm

Länge (L): 92.08mm

Stückgewicht: 0.01 kg



WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

Nordamerika

+1.800.753.9221

Option 1 – Kundendienst

Option 2 – Technischer

Support

Europa

Niederlande:

+31 800-0200135

Frankreich:

+33 800 901 793

Europa

Deutschland:

800 1890272

Sonstige Länder:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

