


Wire Basket Tray PreForm Elbow 90°



The nVent CADDY Wire Basket Tray PreForm Elbow 90° is a precision-engineered solution designed to streamline cable tray installations when a directional change is needed. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Elbow 90° delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Elbow 90° significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

MERKMALE

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Material: Stahl
Oberfläche: Vorverzinkung; Polyurethan



SPEZIFIKATIONEN

Table 1/2


Katalognummer	Farbe	Höhe (H)	Breite (W)	Länge (L)	Lochgröße (HS)	Radius (R)
WBTR902X12		50.8 mm	515.62 mm	515.62mm	19.05 mm	94.64mm
WBTR902X12BA	Schwarz	50.8 mm	515.62 mm	515.62mm	19.05 mm	94.64mm
WBTR902X18		50.8 mm	665.734 mm	665.734mm	19.05 mm	94.64mm
WBTR902X18BA	Schwarz	50.8 mm	665.734 mm	665.734mm	19.05 mm	94.64mm
WBTR902X24		50.8 mm	817.88 mm	817.88mm	19.05 mm	94.64mm
WBTR902X24BA	Schwarz	50.8 mm	817.88 mm	817.88mm	19.05 mm	94.64mm
WBTR902X4		50.8 mm	317.7 mm	317.7mm		94.64mm
WBTR902X4BA	Schwarz	50.8 mm	317.7 mm	317.7mm		94.64mm
WBTR902X6		50.8 mm	365.76 mm	365.76mm		94.64mm

Katalognummer	Farbe	Höhe (H)	Breite (W)	Länge (L)	Lochgröße (HS)	Radius (R)
WBTR902X6BA	Schwarz	50.8 mm	365.76 mm	365.76mm		94.64mm
WBTR902X8		50.8 mm	416.56 mm	416.56mm		94.64mm
WBTR902X8BA	Schwarz	50.8 mm	416.56 mm	416.56mm		94.64mm

Table 2/2

Katalognummer	Stückgewicht	Zertifizierungen
WBTR902X12	1.814 kg	cUL, UL, CE, nVent CADDY Wire Basket Tray System
WBTR902X12BA	1.814 kg	CE, nVent CADDY Wire Basket Tray System
WBTR902X18	3.175 kg	CE, nVent CADDY Wire Basket Tray System, cUL, UL
WBTR902X18BA	3.175 kg	CE, nVent CADDY Wire Basket Tray System
WBTR902X24	4.99 kg	cUL, UL, CE, nVent CADDY Wire Basket Tray System
WBTR902X24BA	4.99 kg	CE, nVent CADDY Wire Basket Tray System
WBTR902X4	0.454 kg	UL, CE, nVent CADDY Wire Basket Tray System, cUL
WBTR902X4BA	0.454 kg	CE, nVent CADDY Wire Basket Tray System
WBTR902X6	0.907 kg	CE, nVent CADDY Wire Basket Tray System, cUL, UL
WBTR902X6BA	0.907 kg	CE, nVent CADDY Wire Basket Tray System
WBTR902X8	0.907 kg	UL, cUL, CE, nVent CADDY Wire Basket Tray System
WBTR902X8BA	0.907 kg	CE, nVent CADDY Wire Basket Tray System

DIAGRAMME



WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

Nordamerika

+1.800.753.9221

Option 1 – Kundendienst

Option 2 – Technischer

Support

Europa

Niederlande:

+31 800-0200135

Frankreich:

+33 800 901 793

Europa

Deutschland:

800 1890272

Sonstige Länder:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. Alle Marken und Logos von nVent sind Eigentum der nVent Services GmbH oder ihrer Tochtergesellschaften oder durch sie lizenziert. Alle übrigen Marken sind Eigentum ihrer jeweiligen Inhaber. nVent behält sich das Recht vor, ohne Vorankündigung Änderungen vorzunehmen.

Dieses Dokument ist systemgeneriert.

