

# Rail Wallmount SRW, EN50125-3 certified

Railway ready EN50125-3 vibration tested pole-mount stainless steel enclosure for integrated wayside radio, fiber splice, access point and power distribution applications.



## MERKMALE

Finish: powder painting UV resistant

Body: Folded and seam welded 1.5 mm/16 gauge thick stainless steel structure, pre-equipped with M8 blind rivet nuts for wall and pole mounting

Door: Corner formed in one piece, 2 mm/14 gauge stainless steel door with 180° left opening with door stopper. Right opening doors available on request

Roof: Rain & Sun hood to protect against adverse weather conditions

Lock: Swing handle with anti-vibration mechanism equipped with DIN profile half cylinder Ronis 2131A lock and Espagnolette two points locking

Cable access: Gland plate on the bottom. Cut-outs can be requested based on project specific requirements

Protection: Up to NEMA Type 12; NEMA Type 13; NEMA Type 4X; IP66; IK10

Internal accessories: Standard: Document Pocket A4; Optional: 19" uprights on the front, Mounting plate in the rear

External accessories: Optional: Lifting eyes, wall/pole mount kits

Additional information: For outdoor environments, the use of a pressure compensation breather is advised. Also in environments known for quick temperature changes, condensation should be taken into consideration. The standard RWS enclosures are delivered with 2 pressure compensation breathers. One under the hood, one on the Gland plate. The pressure compensation breathers are also IP66.

Right opening doors available on request. Gland plate cutouts can be requested based on project specific requirements.

Optional: 19" uprights on the front, Mounting plate in the rear

## SPEZIFIKATIONEN

Table 1/2

| Katalognummer | Höhe Gestell | Höhe  | Breite | Tiefe | Schutzart | Farbe     |
|---------------|--------------|-------|--------|-------|-----------|-----------|
| SRW0604021    | 13U          | 600mm | 400mm  | 210mm | IP66      | Lichtgrau |
| SRW0606021    | 13U          | 600mm | 600mm  | 210mm | IP66      | Lichtgrau |
| SRW0606030    | 13U          | 600mm | 600mm  | 300mm | IP66      | Lichtgrau |
| SRW0806021    | 17U          | 800mm | 600mm  | 210mm | IP66      | Lichtgrau |
| SRW0806030    | 17U          | 800mm | 600mm  | 300mm | IP66      | Lichtgrau |

Table 2/2

| Katalognummer | Farbcode | Anzahl Verpackungen | Entspricht                       | Oberfläche        | Rahmenmaterial |
|---------------|----------|---------------------|----------------------------------|-------------------|----------------|
| SRW0604021    | RAL 7035 | 1                   | EN 50125-3, IEC 62262, IEC 60529 | Pulverbeschichtet | Edelstahl      |
| SRW0606021    | RAL 7035 | 1                   | EN 50125-3, IEC 62262, IEC 60529 | Pulverbeschichtet | Edelstahl      |
| SRW0606030    | RAL 7035 | 1                   | EN 50125-3, IEC 62262, IEC 60529 | Pulverbeschichtet | Edelstahl      |
| SRW0806021    | RAL 7035 | 1                   | EN 50125-3, IEC 62262, IEC 60529 | Pulverbeschichtet | Edelstahl      |
| SRW0806030    | RAL 7035 | 1                   | EN 50125-3, IEC 62262, IEC 60529 | Pulverbeschichtet | Edelstahl      |

## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

#### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

#### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

#### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

#### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



©2026 nVent. Alle Marken und Logos von nVent sind Eigentum der nVent Services GmbH oder ihrer Tochtergesellschaften oder durch sie lizenziert. Alle übrigen Marken sind Eigentum ihrer jeweiligen Inhaber. nVent behält sich das Recht vor, ohne Vorankündigung Änderungen vorzunehmen.

Dieses Dokument ist systemgeneriert.