

Wire Basket Tray Center Support



The nVent CADDY Wire Basket Tray Center Support is a simple and efficient way to support wire basket trays from a single threaded rod. The offset center tube helps ensure the tray is centered and secured, enhancing both structural integrity and improving project efficiency. Designed for light-duty cable support projects, installation is easy—simply hold the Center Support parallel to the tray, then turn perpendicular until you hear the Center Support lock into place.

Compatible with varying nVent CADDY Wire Basket Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

MERKMALE

Use as a central support when hanging with threaded rod

Designed to be used with the nVent CADDY Wire Basket Tray Splice Kit


Supported with 3/8 or 1/2 in threaded rod

Material: Stahl
Oberfläche: Elektrolytisch verzinkt



SPEZIFIKATIONEN

Katalognummer	Farbe	Höhe (H)	Breite (W)	Länge (L)	Lochgröße (HS)	Stückgewicht
WBTCTSPRT12		193.55 mm	41.4 mm	292.176mm	15.75 mm	1.225 kg
WBTCTSPRT4		193.55 mm	41.4 mm	105.156mm	15.75 mm	0.7 kg
WBTCTSPRT4BA	Schwarz	193.55 mm	41.4 mm	105.156mm	15.75 mm	0.7 kg
WBTCTSPRT6		193.55 mm	41.4 mm	147.777mm	15.75 mm	0.816 kg
WBTCTSPRT8		193.55 mm	41.4 mm	190.551mm	15.75 mm	0.907 kg



WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

Nordamerika

+1.800.753.9221

Option 1 – Kundendienst

Option 2 – Technischer

Support

Europa

Niederlande:

+31 800-0200135

Frankreich:

+33 800 901 793

Europa

Deutschland:

800 1890272

Sonstige Länder:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

