


# Wire Basket Tray PreForm Intersection



The nVent CADDY Wire Basket Tray PreForm Intersection is a precision-engineered solution designed to streamline cable tray installations at multi-pathway junctions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Intersection delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Intersection significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

## MERKMALE

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

**Material:** Stahl  
**Oberfläche:** Vorverzinkung; Polyurethan



## SPEZIFIKATIONEN

Table 1/2


| Katalognummer | Farbe   | Höhe (H) | Breite (W) | Länge (L) | Lochgröße (HS) | Radius (R) |
|---------------|---------|----------|------------|-----------|----------------|------------|
| WBTI2X12      |         | 50.8 mm  | 711.2 mm   | 711.2mm   | 19.05 mm       | 94.64mm    |
| WBTI2X12BA    | Schwarz | 50.8 mm  | 711.2 mm   | 711.2mm   | 19.05 mm       | 94.64mm    |
| WBTI2X18      |         | 50.8 mm  | 861.06 mm  | 861.06mm  | 19.05 mm       | 94.64mm    |
| WBTI2X18BA    | Schwarz | 50.8 mm  | 861.06 mm  | 861.06mm  | 19.05 mm       | 94.64mm    |
| WBTI2X24      |         | 50.8 mm  | 1016 mm    | 1016mm    | 19.05 mm       | 94.64mm    |
| WBTI2X24BA    | Schwarz | 50.8 mm  | 1016 mm    | 1016mm    | 19.05 mm       | 94.64mm    |
| WBTI2X4       |         | 50.8 mm  | 511.48 mm  | 511.48mm  |                | 94.64mm    |
| WBTI2X4BA     | Schwarz | 50.8 mm  | 511.48 mm  | 511.48mm  |                | 94.64mm    |
| WBTI2X6       |         | 50.8 mm  | 561.34 mm  | 561.34mm  |                | 94.64mm    |

| Katalognummer | Farbe   | Höhe (H) | Breite (W) | Länge (L) | Lochgröße (HS) | Radius (R) |
|---------------|---------|----------|------------|-----------|----------------|------------|
| WBTI2X6BA     | Schwarz | 50.8 mm  | 561.34 mm  | 561.34mm  |                | 94.64mm    |
| WBTI2X8       |         | 50.8 mm  | 612.14 mm  | 612.14mm  |                | 94.64mm    |
| WBTI2X8BA     | Schwarz | 50.8 mm  | 612.14 mm  | 612.14mm  |                | 94.64mm    |

Table 2/2

| Katalognummer | Stückgewicht | Zertifizierungen                                 |
|---------------|--------------|--------------------------------------------------|
| WBTI2X12      | 3.175 kg     | UL, CE, nVent CADDY Wire Basket Tray System, cUL |
| WBTI2X12BA    | 3.175 kg     | CE, nVent CADDY Wire Basket Tray System          |
| WBTI2X18      | 5.443 kg     | CE, nVent CADDY Wire Basket Tray System, UL, cUL |
| WBTI2X18BA    | 5.443 kg     | CE, nVent CADDY Wire Basket Tray System          |
| WBTI2X24      | 8.165 kg     | UL, CE, nVent CADDY Wire Basket Tray System, cUL |
| WBTI2X24BA    | 8.165 kg     | CE, nVent CADDY Wire Basket Tray System          |
| WBTI2X4       | 0.907 kg     | CE, nVent CADDY Wire Basket Tray System, UL, cUL |
| WBTI2X4BA     | 0.907 kg     | CE, nVent CADDY Wire Basket Tray System          |
| WBTI2X6       | 1.361 kg     | cUL, CE, nVent CADDY Wire Basket Tray System, UL |
| WBTI2X6BA     | 1.361 kg     | CE, nVent CADDY Wire Basket Tray System          |
| WBTI2X8       | 2.268 kg     | UL, cUL, CE, nVent CADDY Wire Basket Tray System |
| WBTI2X8BA     | 2.268 kg     | CE, nVent CADDY Wire Basket Tray System          |

## DIAGRAMME



## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

#### **Nordamerika**

+1.800.753.9221

Option 1 – Kundendienst

Option 2 – Technischer

Support

#### **Europa**

Niederlande:

+31 800-0200135

Frankreich:

+33 800 901 793

#### **Europa**

Deutschland:

800 1890272

Sonstige Länder:

+31 13 5835404

#### **APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. Alle Marken und Logos von nVent sind Eigentum der nVent Services GmbH oder ihrer Tochtergesellschaften oder durch sie lizenziert. Alle übrigen Marken sind Eigentum ihrer jeweiligen Inhaber. nVent behält sich das Recht vor, ohne Vorankündigung Änderungen vorzunehmen.

Dieses Dokument ist systemgeneriert.

