

ABP Perforated Strap with Rounded Edge, Standard Duty

FEATURES

Steel perforated mounting strap

Enclosed in plastic case



SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Width	Length	Thickness
ABP12PG	583920	Steel	Pregalvanized	12 mm	10m	0.8 mm
ABP12S4	584020	Stainless Steel 304 (EN 1.4301)		12 mm	10m	0.8 mm
ABP17PG	583930	Steel	Pregalvanized	17 mm	10m	0.8 mm
ABP26PG	583940	Steel	Pregalvanized	26 mm	10m	1 mm

Table 2/2

Catalog Number	Article Number	Hole Size	Static Load
ABP12PG	583920	5 mm	560N
ABP12S4	584020	5 mm	700N
ABP17PG	583930	7 mm	800N
ABP26PG	583940	8 mm	1800N

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

