

C-Channel U-Shaped Washer

FEATURES

U-shaped wrap around washer



For use with C-Profiles



Material: Steel
Finish: Electrogalvanized

SPECIFICATIONS

Catalog Number	Article Number	A	B	C	Thickness (T)	Hole Size (HS)	Channel Type
PLNE008	588240	28 mm	30 mm	15 mm	2 mm	8.5 mm	E0, E0L
PLNE010	588250	28 mm	30 mm	15 mm	2 mm	10.5 mm	E0, E0L
PLNE1208	588260	31 mm	30 mm	13.5 mm	2 mm	8.5 mm	E0L, E0, E1
PLNE3408	588280	39 mm	30 mm	17.5 mm	3 mm	8.5 mm	E2, E3, E4
PLNE3410	588285	39 mm	30 mm	17.5 mm	3 mm	10.5 mm	E2, E3, E4
PLUNI10	588290	35 mm	30 mm	10 mm	3 mm	10.5 mm	E1, E2, E2L



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

