

Improved Cat HP J-hook, 25 mm, with Hammer-On Flange Clip Swivel, 3–8 mm Flange

CATALOG NUMBER

CAT16HP24



The Improved nVent CADDY Cat HP J-Hook with Hammer-On Flange Clip, Swivel is an innovative assembly featuring a combination of the Improved nVent CADDY Cat HP J-Hook with a Hammer-On Flange Clip, Swivel attachment. With a 360-degree rotation, this solution supports flexible cable routing, while rounded edges maintain proper bend radius for high-performance data cables including Cat 5e through Cat 7 and fiber optic. Installers can simplify setup and improve productivity by eliminating screws, rivets, and special tools. Engineered for strength and efficiency, the Assembly delivers superior fill capacity and securely clips onto beam flanges.

FEATURES

Requires only a hammer to install

Rotates 360 degrees to support various directional runs of cable

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



PRODUCT ATTRIBUTES

Article Number: 181213

Material: Steel;Spring Steel

Finish: Pregalvanized;nVent CADDY Armour

Diameter: 25 mm

Area: 690mm²

Cable Capacity, Cat 5e: 20

Cable Capacity, Cat 6: 15

Cable Capacity, Cat 6A: 10

Flange Thickness: 3 - 8 mm

Static Load: 270N

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

