

EER-Ti/T Trapezoidal Deck Threaded Rod Hanger, M6 Hole, Threaded, 0.8–3 mm Flange



CATALOG NUMBER

EERTIM6

FEATURES

Supports threaded rod

Thread impression for simple installation

PRODUCT ATTRIBUTES

Article Number: 173120

Material: Spring Steel

Finish: nVent CADDY Armour

Hole Size (HS): 6 mm

Hole Type: Threaded

Flange Thickness (FT): 0.8 - 3 mm

Drill Bit Diameter: 7mm

Static Load 1 (F1): 450N

Static Load 2 (F2): 900N

ADDITIONAL PRODUCT DETAILS

Static Load 1 represents 0.8 - 2.0 mm flange thickness. Static Load 2 represents 2.0 - 3.0 mm flange thickness.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

