

H-Ti/T Rod to Flange Clip, M10 Hole, Threaded, 8–14 mm Flange



CATALOG NUMBER

M10TI58

FEATURES

Suspends threaded rod from beam flanges

Threaded rod hanger can swivel to provide a vertical dropdown

Requires only a hammer to install



PRODUCT ATTRIBUTES

Article Number: 175010

Material: Spring Steel

Finish: nVent CADDY Armour

Hole Size (HS): 10 mm

Hole Type: Threaded

Flange Thickness (FT): 8 - 14 mm

Static Load: 900N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

