

Strut Beam Clip, Steel, HDG, 16 mm Max Flange, 13 mm Hole



CATALOG NUMBER

ZTA605

FEATURES

- Beam Clip for clamping the open side of strut to a beam
- Suitable for all strut channels
- Requires installation in pairs
- Structural attachment to beams to support nVent CADDY Eristrut
- FM® Specification Tested

PRODUCT ATTRIBUTES

Article Number: 388080

Material: Steel

Finish: Hot-Dip Galvanized

Flange Thickness (FT): 16 mm Max

Hole Size (HS): 13 mm

Length (L): 49mm

Thickness (T): 6 mm


Width (W): 40 mm

Static Load: 2040N

Screw Included: No

ADDITIONAL PRODUCT DETAILS

Indicated loads are based on installation with 1/2" (M12) hardware and strut channel type A.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

