

Improved nVent CADDY Cat HP J-Hook with Pedestal Clamp



The Improved nVent CADDY Cat HP J-Hook with Pedestal Clamp is an innovative assembly featuring a combination of the Improved nVent CADDY Cat HP J-Hook with a Pedestal Clamp attachment. The Assembly simplifies cable management by offering quick installation to pedestals under raised floors.

Engineered for high-performance data cable management, this system supports Cat 5e, Cat 6, Cat 6A, Cat 7, and fiber optic cables with superior fill capacity and load ratings compared to most non-continuous alternatives. The Assemblies' rounded edges ensure proper bend radius support, protecting cable integrity and optimizing performance.

FEATURES

Listed for use with flexible conduit, cable or tubing

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, raised floors and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Diameter	Area	Cable Capacity, Cat 5e
CAT32HPCD1B	181227	Steel	Pregalvanized	50 mm	2561mm ²	90
CAT48HPCD1B	181228	Steel	Pregalvanized	75 mm	5974mm ²	200
CAT64HPCD1B	181229	Steel	Pregalvanized	100 mm	9987mm ²	330

Table 2/2

Catalog Number	Article Number	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	Pedestal Size
CAT32HPCD1B	181227	60	35	19 mm Square, 22.2 - 28.5 mm Round
CAT48HPCD1B	181228	150	80	19 mm Square, 22.2 - 28.5 mm Round
CAT64HPCD1B	181229	220	140	19 mm Square, 22.2 - 28.5 mm Round

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

