

Threaded Rod, Steel, EG, M6 Rod, 2,000 mm

CATALOG NUMBER

050M62000

FEATURES

Cut to length as needed

According to standard DIN 976-1 / ISO 7412

Property Class 4.8



PRODUCT ATTRIBUTES

Article Number: 592580

Material: Steel


Finish: Electrogalvanized

Quality Class: 4.8

Rod Size (RS): M6

Length (L): 2000mm

Static Load: 2400N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

