

H-MSM Conduit/Pipe to Flange Clip, Side Mount, 23.4–35mm OD, 8–14mm Flange



CATALOG NUMBER

16M58SM

FEATURES

Supports conduit/pipe or cable from beam flanges

Snap close clip pivots a full 360°

Requires only a hammer to install



PRODUCT ATTRIBUTES

Article Number: 173730


Material: Spring Steel

Finish: nVent CADDY Armour

Outer Diameter (OD): 23.4 - 35 mm

Flange Thickness (FT): 8 - 14 mm

Static Load: 120N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

