

Heavy Duty Strut Beam Clamp, Steel, Hot-dip galvanized, 3–33 mm Flange



CATALOG NUMBER

6120HD

FEATURES

Suitable for strut mounting

PRODUCT ATTRIBUTES

Article Number: 330600

Material: Steel

Finish: Hot-Dip Galvanized

Flange Thickness (FT): 3 - 33 mm

B: 60 mm

Torque (TQ): 30 N·m

Strut Type	A	Static Load 1 F1	Static Load 2 F2
CC	200 mm	4000 N	1100 N
	300 mm	3000 N	750 N
	400 mm	2250 N	550 N
	500 mm	1800 N	450 N
	600 mm	1500 N	350 N
AA	200 mm	7000 N	3250 N
	300 mm	7000 N	2250 N
	400 mm	7000 N	1750 N
	500 mm	5500 N	1400 N
	600 mm	4500 N	1150 N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
 +1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe
 Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe
 Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC
 Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500

