

C-ES Cable to Vertical Flange Clamp, 6–12 mm OD



CATALOG NUMBER

C12ES

FEATURES

Supports single run of cable

Attaches to beam flanges, angle iron, joists and other structural supports

PRODUCT ATTRIBUTES

Article Number: 337000

Material: Steel

Finish: Hot-Dip Galvanized

Outer Diameter (OD): 6 - 12 mm

A: 43 mm

Torque (TQ): 2 N·m

ADDITIONAL PRODUCT DETAILS

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

