

Gravity Toggle with Rubber Washer, M10 Rod, 200 mm

CATALOG NUMBER

MTVB10200

FEATURES

Complete with rod, nut, washer and load distribution block

Threaded rod is secured against unintentional removal

Approved for use in stationary fire protection systems (for pipes up to 2")



PRODUCT ATTRIBUTES

Article Number: 584466

Material: Steel

Finish: Electrogalvanized

Rod Size (RS): 10

Length (L): 200mm

Drill Bit Diameter: 25mm


Static Load: 800N

Ultimate Static Load (F): 20kN

ADDITIONAL PRODUCT DETAILS

Static Load represents the maximum recommended load when fixed to a trapezoidal sheet.

The Ultimate Static Load value does not take into account the load-bearing characteristics of the supporting material. The appropriate safety factor is to be added to this load rating.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

