

OCDC-Ti/T Deck Threaded Rod Hanger, M6 Hole, Threaded, 1–2.5 mm Flange

CATALOG NUMBER

OCDCTIM6

FEATURES

Attaches to decking without having to drill or punch holes

Supports threaded rod



PRODUCT ATTRIBUTES

Article Number: 160710

Material: Spring Steel

Finish: nVent CADDY Armour

Hole Size (HS): 6 mm

Hole Type: Threaded

Flange Thickness (FT): 1.0 - 2.5 mm

Static Load: 400N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

