

nVent CADDY Speed Link SLK with Drop Wire Clip, 3 mm Wire, 1 m Length

CATALOG NUMBER

SLK3L1DW6

FEATURES

Complete system includes wire, locking device and pre-assembled drop wire clip end fitting for catenary cable

Can be used to hang services from catenary cable or act as an intermediate support to reduce sag and tension

Easily snaps onto catenary cable and locks in place when closed

Tool-free clip can be hand-closed on the catenary wire



PRODUCT ATTRIBUTES

Article Number: 196842

Material: Steel;Spring Steel;Polypropylene;Zinc Alloy

Finish: Electrogalvanized;nVent CADDY Armour

Static Load Safety Factor: 5:1

Wire Rope Diameter: 3 mm

Wire Rope Length: 1m

A: 70 mm

B: 20 mm

C: 25 mm

Diameter (Ø): 6 mm

Height (H): 62 mm

Width (W): 24 mm

Thickness (T): 16 mm

Angle (a): 90 ° Max

Static Load: 700N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

