

PX NI Heavy Duty Pipe Clamp with External Thread

FEATURES

Includes male/female combination nut

Heavy duty



Nut Included: Yes

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Outer Diameter (OD)	NB/D N	Rod Size (RS)
PXN025EG	577060	Steel	Electrogalvanized	21 - 25 mm	15	M10
PXN025S6	577460	Stainless Steel 316 (EN 1.4401)		21 - 25 mm	15	M10
PXN031EG	577070	Steel	Electrogalvanized	26 - 31 mm	20	M10
PXN031S6	577470	Stainless Steel 316 (EN 1.4401)		26 - 31 mm	20	M10
PXN036EG	577080	Steel	Electrogalvanized	32 - 36 mm	25	M10
PXN036S6	577480	Stainless Steel 316 (EN 1.4401)		32 - 36 mm	25	M10

Catalog Number	Article Number	Material	Finish	Outer Diameter (OD)	NB/D N	Rod Size (RS)
PXN046EG	577100	Steel	Electrogalvanized	41 - 46 mm	32	M10
PXN046S6	577500	Stainless Steel 316 (EN 1.4401)		41 - 46 mm	32	M10
PXN052EG	577110	Steel	Electrogalvanized	47 - 52 mm	40	M10
PXN052S6	577510	Stainless Steel 316 (EN 1.4401)		47 - 52 mm	40	M10
PXN063EG	577130	Steel	Electrogalvanized	59 - 63 mm	50	M10
PXN063S6	577530	Stainless Steel 316 (EN 1.4401)		59 - 63 mm	50	M10
PXN073EG	577150	Steel	Electrogalvanized	70 - 73 mm		M10
PXN079EG	577160	Steel	Electrogalvanized	74 - 79 mm	65	M10
PXN079S6	577560	Stainless Steel 316 (EN 1.4401)		74 - 79 mm	65	M10
PXN092EG	577180	Steel	Electrogalvanized	87 - 92 mm	80	M10
PXN092S6	577580	Stainless Steel 316 (EN 1.4401)		87 - 92 mm	80	M10
PXN105S6	577600	Stainless Steel 316 (EN 1.4401)		100 - 105 mm		M10
PXN117EG	577220	Steel	Electrogalvanized	112 - 117 mm	100	M10
PXN117S6	577620	Stainless Steel 316 (EN 1.4401)		112 - 117 mm	100	M10

Table 2/2

Catalog Number	Article Number	Material	Finish	Outer Diameter (OD)	NB/D N	Rod Size (RS)
PXN143S6	577660	Stainless Steel 316 (EN 1.4401)		137 - 143 mm	125	M12
PXN163S6	577690	Stainless Steel 316 (EN 1.4401)		157 - 163 mm		M12
PXN169EG	577300	Steel	Electrogalvanized	164 - 169 mm	150	M12
PXN169S6	577700	Stainless Steel 316 (EN 1.4401)		164 - 169 mm	150	M12

Catalog Number	Article Number	Material	Finish	Outer Diameter (OD)	NB/D N	Rod Size (RS)
PXN175S6	577710	Stainless Steel 316 (EN 1.4401)		170 - 175 mm		M12
PXN182S6	577720	Stainless Steel 316 (EN 1.4401)		176 - 182 mm		M12
PXN205S6	577750	Stainless Steel 316 (EN 1.4401)		199 - 205 mm		M12
PXN219S6	577770	Stainless Steel 316 (EN 1.4401)		213 - 219 mm	200	M12
PXN252EG	577400	Steel	Electrogalvanized	246 - 252 mm		M12
PXN252S6	577800	Stainless Steel 316 (EN 1.4401)		246 - 252 mm		M12



Table 1/2

Catalog Number	Article Number	Gewinde (G)	Width (W)	Thickness (T)	Screw Diameter (Sc)	Screw Length (L)	Static Load
PXN025EG	577060	1/2"	27 mm	2.2 mm	6	20mm	2500N
PXN025S6	577460	1/2"	27 mm	2 mm	6	20mm	2500N
PXN031EG	577070	1/2"	27 mm	2.2 mm	6	20mm	2500N
PXN031S6	577470	1/2"	27 mm	2 mm	6	20mm	2500N
PXN036EG	577080	1/2"	27 mm	2.2 mm	6	20mm	2500N
PXN036S6	577480	1/2"	27 mm	2 mm	6	20mm	2500N
PXN046EG	577100	1/2"	27 mm	2.2 mm	6	20mm	2500N
PXN046S6	577500	1/2"	27 mm	2 mm	6	20mm	2500N
PXN052EG	577110	1/2"	27 mm	2.2 mm	6	25mm	2500N
PXN052S6	577510	1/2"	27 mm	2 mm	6	20mm	2500N
PXN063EG	577130	1/2"	27 mm	2.2 mm	6	25mm	2500N
PXN063S6	577530	1/2"	27 mm	2 mm	6	20mm	2500N
PXN073EG	577150	1/2"	27 mm	2.2 mm	6	25mm	2500N
PXN079EG	577160	1/2"	31 mm	2.5 mm	6	25mm	2500N
PXN079S6	577560	1/2"	31 mm	2 mm	8	25mm	2500N
PXN092EG	577180	1/2"	31 mm	2.5 mm	6	25mm	2500N
PXN092S6	577580	1/2"	31 mm	2 mm	8	25mm	2500N
PXN105S6	577600	1/2"	31 mm	2 mm	8	25mm	2500N
PXN117EG	577220	1/2"	31 mm	2.5 mm	6	25mm	2500N
PXN117S6	577620	1/2"	31 mm	2 mm	8	25mm	2500N

Table 2/2

Catalog Number	Article Number	Gewinde (G)	Width (W)	Thickness (T)	Screw Diameter (Sc)	Screw Length (L)	Static Load
PXN143S6	577660	3/4"	38 mm	2.5 mm	8	30mm	3500N
PXN163S6	577690	3/4"	38 mm	2.5 mm	8	30mm	3500N
PXN169EG	577300	3/4"	38 mm	2.9 mm	8	30mm	3500N
PXN169S6	577700	3/4"	38 mm	2.5 mm	8	30mm	3500N
PXN175S6	577710	3/4"	38 mm	2.5 mm	8	30mm	3500N
PXN182S6	577720	3/4"	38 mm	2.5 mm	8	30mm	3500N
PXN205S6	577750	3/4"	38 mm	2.5 mm	8	30mm	3500N
PXN219S6	577770	3/4"	38 mm	2.5 mm	8	30mm	3500N
PXN252EG	577400	3/4"	38 mm	2.9 mm	8	30mm	3500N
PXN252S6	577800	3/4"	38 mm	2.5 mm	8	30mm	3500N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

