

Wire Rope Cutter



FEATURES

Designed to cut steel stranded wires

Special blade design reduces wire rope fraying

With anti-jamming mechanism

SPECIFICATIONS

Catalog Number	Article Number	Material	Brace Size	Cable Diameter	Length
CSBC48	402536	Steel	#36	6mm	600mm

ADDITIONAL PRODUCT DETAILS

For brace sizes #12 and #18 use SLWC Wire Rope Cutter.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

