

Casters, LCR

These casters will make a fully equipped enclosure movable within a facility.

FEATURES

Description: For easy transportation of an (equipped) enclosure. Can be mounted directly to the enclosure's frame or underneath the plinths (PF/PV) with the provided mounting brackets. Raises the enclosure by 70 mm.

Maximum load: 2800 N (Moving) or 5600 N (Static) per kit.

Pack quantity: 4 pieces with mounting accessories.



Material: Plastic; Plastic

Finish: Plated

SPECIFICATIONS

Catalog Number	Height	Width	Depth	Caster Quantity	Brakes Included	Product Family
LCR470	73mm	102mm	80mm	4	No	Free-Standing, Human Machine Interface
LCR471	73mm	102mm	80mm	4	Yes	Free-Standing, Human Machine Interface
LCR472	73mm	102mm	80mm	4	Yes	Free-Standing, Human Machine Interface

ADDITIONAL PRODUCT DETAILS

ENC_LCR471 contains 2 casters with brakes and 2 without brakes

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.