

BC-M Conduit to Beam Clamp



FEATURES

Easy installation to beam flanges

Eliminates offset bending conduit


Conduit clip rotates 360 degrees

Material: Spring Steel
Finish: nVent CADDY Armour



SPECIFICATIONS

Catalog Number	Article Number	Outer Diameter (OD)	Flange Thickness (FT)	Torque (TQ)	Static Load
EBC16M	172590	23.4 - 35 mm	16 mm Max	3 N·m	450N
EBC20M	172600	35 - 42 mm	16 mm Max	3 N·m	450N
EBC24M	172610	42 - 50 mm	16 mm Max	3 N·m	450N
EBC32M	172620	50 - 60 mm	16 mm Max	3 N·m	450N
EBC812M	160200	18 - 30 mm	16 mm Max	3 N·m	450N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

