

BC-MSM Conduit to Beam Clamp, Side Mount



FEATURES

Easy installation to beam flanges

Eliminates offset bending conduit


Conduit clip rotates 360 degrees

Material: Spring Steel
Finish: nVent CADDY Armour



SPECIFICATIONS

Catalog Number	Article Number	Outer Diameter (OD)	Flange Thickness (FT)	Torque (TQ)	Static Load
EBC16MSM	172660	23.4 - 35 mm	16 mm Max	3 N·m	110N
EBC20MSM	172670	35 - 42 mm	16 mm Max	3 N·m	110N
EBC24MSM	172680	42 - 50 mm	16 mm Max	3 N·m	110N
EBC32MSM	172690	50 - 60 mm	16 mm Max	3 N·m	110N
EBC812MSM	160180	18 - 30 mm	16 mm Max	3 N·m	110N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

