


Wire Basket Tray Vertical Down



The nVent CADDY Wire Basket Tray Vertical Down maintains the proper bend radius of high-performance cables as they transition from the end or side of the cable tray. This offering enables smooth wire transfers from horizontal to vertical angles, ensuring cable integrity and optimizing organization. Easily assembled with the nVent CADDY Wire Basket Tray Splice Kit, the Vertical Down is ideal for small cable runs directed to data cabinets and enclosures. Contractors can experience optimal and reliable management for vertical cable dropouts while maintaining a seamless and visually appealing finished result.

FEATURES

Designed to be used with the nVent CADDY Wire Basket Tray Splice Kit

Ensures the natural bend radius of the cable is protected


Provides optimal support for high-performance data cable, up to and including fiber optic, Cat 5e, Cat 6, Cat 6A, and Cat 7

Material: Steel
Finish: Electrogalvanized

SPECIFICATIONS

Catalog Number	Color	Height (H)	Width (W)	Length (L)	Radius (R)	Unit Weight
WBTVERTDWN		66 mm	172 mm	200mm	64.52mm	0.84 kg
WBTVERTDWNBA	Black	66 mm	172 mm	200mm	64.52mm	0.84 kg
WBTVERTDWNWH	White	66 mm	172 mm	200mm	64.52mm	0.84 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

