


nVent ERIFLEX Flexibar End Cover



FEATURES

- End cover for nVent ERIFLEX Flexibar and Insulated Power Braid
- Allows for visual inspection of connection
- Easy fitting after fixing
- Halogen free
- RoHS compliant

Material: Polycarbonate
Flammability Rating: UL® 94V-0



SPECIFICATIONS

Catalog Number	Article Number	Conductor Width	Unit Weight
ENDCOV20	541774	20 mm	0.19 kg
ENDCOV24	541775	24 mm	0.22 kg
ENDCOV32	541776	32 mm	0.26 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.