

FCS Height Adjustable Loop Hanger, 4" Pipe, DN100, 114 mm, M10 Rod



CATALOG NUMBER

FCS0400M10

FEATURES

Recommended for the suspension of stationary non-insulated fire sprinkler pipe

Redesigned strap and cup nut minimize friction for easier adjustment up and down the threaded rod (1/2" to 4" sizes)

Formed tips on the upper strap simplify disassembly and reassembly of the hanger

Rolled edges on the strap help to guide the pipe through, limiting binding and damage to metal or plastic pipe

Package includes all necessary hardware for installation



PRODUCT ATTRIBUTES

Article Number: 597976

Material: Steel

Finish: Electrogalvanized

Pipe Size: 4"

NB/DN: 100

Outer Diameter (OD): 114 mm

Rod Size (RS): M10

Width (W): 10 mm

A: 206 mm

B: 112 mm

C: 55 mm

Static Load: 3500N

Wrench Size: 15 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

