

nVent CADDY Speed Link Catenary Cable Spool, 50 m Length

CATALOG NUMBER

SLC6L50

FEATURES

Used for installing custom lengths of catenary cable with two locking devices

Spool with nVent CADDY Speed Link steel wire

Wire rope constructed from 7 bundles of 19 strands each of steel aircraft wire



PRODUCT ATTRIBUTES

Article Number: 196821

Material: Steel

Finish: Hot-Dip Galvanized

Wire Rope Diameter: 6 mm

Wire Rope Length: 50m

Angle (a): 60 ° Max

ADDITIONAL PRODUCT DETAILS

Static load 1 represents a point load in the center of the catenary installation. Static load 2 represents a two or three point distributed load on the catenary installation. Static load 3 represents a four or more point distributed load on the catenary installation.

Preload of the wire rope must be applied using Catenary Tensioning Tool.

Cut-to-order (CTO) lengths orderable in meter increments.

Horizontal Intallation		
Preload	1000 N	450 N
Static Load 1 (F1)	490 N	590 N
Static Load 2 (F2)	880 N	1080 N
Static Load 3 (F3)	980 N	1180 N
Vertical Installation		
Static Load 4 (F4)	4440 N	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
 +1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical
 Support

Europe
 Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe
 Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC
 Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500

