

Wire Basket Tray Ceiling Support



In the evolving landscape of cable management, the nVent CADDY Wire Basket Tray Ceiling Support is a simple and efficient alternative to traditional strut trapeze systems for wire basket tray installations. Engineered for simplicity and strength, this support solution not only anchors wire basket trays securely to the ceiling but also doubles as a splice point—making it a dual-function component that enhances both structural integrity and installation efficiency.

Compatible with varying nVent CADDY Wire Basket Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

FEATURES

Use as a center support or support provisioned from both ends

Designed to be used with the nVent CADDY Wire Basket Tray Ground Splice and nVent CADDY Wire Basket Tray Splice Kit

Supported with 3/8 or 1/2 in threaded rod

Material: Steel




SPECIFICATIONS

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Unit Weight
WBTCLSPRT12	Electrogalvanized		15.75 mm	41.4 mm	388.417mm	13.49 mm	0.499 kg
WBTCLSPRT12BA	Electrogalvanized	Black	15.75 mm	41.4 mm	388.417mm	13.49 mm	0.499 kg
WBTCLSPRT18	Electrogalvanized		15.75 mm	41.4 mm	538.226mm	13.49 mm	0.726 kg
WBTCLSPRT18BA	Electrogalvanized	Black	15.75 mm	41.4 mm	538.226mm	13.49 mm	0.726 kg
WBTCLSPRT24	Electrogalvanized		15.75 mm	41.4 mm	688.442mm	13.49 mm	0.862 kg
WBTCLSPRT24BA	Electrogalvanized	Black	15.75 mm	41.4 mm	688.442mm	13.49 mm	0.862 kg

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Unit Weight
WBTCLSPRT6	Pregalvanized		15.75 mm	41.4 mm	238.404mm	13.49 mm	0.249 kg
WBTCLSPRT6BA	Pregalvanized	Black	15.75 mm	41.4 mm	238.404mm	13.49 mm	0.249 kg
WBTCLSPRT8	Pregalvanized		15.75 mm	41.4 mm	288.392mm	13.49 mm	0.363 kg
WBTCLSPRT8BA	Pregalvanized	Black	15.75 mm	41.4 mm	288.392mm	13.49 mm	0.363 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America +1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support	Europe Netherlands: +31 800-0200135 France: +33 800 901 793	Europe Germany: 800 1890272 Other Countries: +31 13 5835404	APAC Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500
---	--	--	--

